



Lens Protection Discs

OptiSafe Anti-Slip Pad

Provides excellent adhesion to oleophobic and super hydrophobic premium lens coatings. Apply pad to clean lens surface prior to applying blocking pad to prevent lens from "twisting" and "slipping" off-axis while edging.

30x40 mm, 500 pads/box, *Item #T1100*
 25x40 mm, 500 pads/box, *Item #T1125*
 19x40 mm, 500 pads/box, *Item #T1119*



Ultra-Grip Anti-Slip Pad

Provides excellent adhesion to Higher oleophobicity premium lens coatings. Apply pad to clean lens surface prior to applying blocking pad to prevent lens from "twisting" and "slipping" off-axis while edging.

26x40 mm, 500 pads/box, *Item #T1130*
 19x40 mm, 500 pads/box, *Item #T1139*



PH-T1100-0315

(800) 225-5559 U.S.A.
 +1-619-449-7754 International

www.phantomresearch.com
 email: sales@phantomresearch.com

65

Lens Protection Discs

Ultra-Hold Anti-Slip Pad

Provides excellent adhesion to very High oleophobicity premium lens coatings. Apply pad to clean lens surface prior to applying blocking pad to prevent lens from "twisting" and "slipping" off-axis while edging.

24x38 mm, 500 pads/box, *Item #T1142*



OptiSafe 22 MM Blue Lens Protection Disc

22 mm blue disc to prevent lens surface from scratching during hand edging, grooving, faceting, drilling, polish edging, and also when handling/shipping of lenses. Apply to both sides of lens.

Tab for easy removal, no residues
 22mm, pre-cut
 1000 discs/roll, *Item #TG899*
 2000 discs/roll, *Item #TG900*



OptiSafe 35 MM Blue Lens Protection Disc

35 mm blue disc to prevent lens surface from scratching during hand edging, grooving, faceting, drilling, polish edging, and also when handling/shipping of lenses. Apply to both sides of lens.

Tab for easy removal, no residues
 35mm, pre-cut
 2000 discs/roll, *Item #T1647*



OptiSafe 22mm Clear Lens Protection Disc

22 mm Clear disc to prevent lens surface from scratching during hand edging, grooving, faceting, drilling, polish edging, and also when handling/shipping of lenses. Apply to both sides of lens.

Tab for easy removal, no residues.
 22mm, pre-cut
 1000 discs/roll, *Item #TG844*



PH-TG901-0315

(800) 225-5559 U.S.A.
 +1-619-449-7754 International

www.phantomresearch.com
 email: sales@phantomresearch.com

66